



1.1
1.2
1.3
1.4

1 d ₁	2 d ₂	3 Länge l				d ₃	b	h	t min.
25	M 6	16	20	25	-	8	8	10	7
30	M 6	16	20	25	-	10	10	12	7
30	M 8	16	20	25	32	10	10	12	9
36	M 8	16	20	25	32	12	12	14,5	9
36	M 10	20	30	40	-	12	12	14,5	7

Ausführung

- Kopf
 - Edelstahl (Sinterstahl)
 - nichtrostend, 1.4404
 - matt gestrahlt
- Schraube
 - Edelstahl
 - nichtrostend, 1.4301
 - matt gestrahlt
 - eingeschraubt und mit Querstift gesichert
- *Edelstahl-Eigenschaften* → Seite 1883
- RoHS

Hinweis

- siehe auch...
- *Edelstahl-Flügelmuttern GN 834* → Seite 578
 - *Edelstahl-Flügelerschrauben GN 835* → Seite 579

2.1
2.2
2.3
2.4

Bestellbeispiel (Innengewinde)	1 d ₁
	2 d ₂

Bestellbeispiel (Schraube)	1 d ₁
	2 d ₂
	3 Länge l