



ROSTFREI
Inox
Stainless
Steel

4 Type
A without bores

2

3

l_1	l_2	d	h	s
60	30	6	12	3
60	40	6	12	3
60	60	6	12	3
80	30	6	12	3
80	40	6	12	3
80	80	6	12	3
100	100	6	12	3

Specification

1

5

- Stainless Steel **NI**
- AISI 304
- blank **BL**
- Pin
- Stainless Steel AISI 304
- riveted
- Stainless Steel characteristics → Page 1489
- Load rating information of metal hinges → Page XYZ
- RoHS

On request

- other dimensions
- with bores
- other surface types

Information

Stainless Steel-Sheet metal hinges GN 1362 are distinguished by their universally compatible dimensions. The materials used also permit applications in aggressive environments.

Type A is fastened via welding or holes created by the customer.

Thanks to the standard dimensions, special application-specific solutions can be realized even in relatively small quantities.

see also...

- List of hinge types → Page XYZ ff.
- Sheet metal hinges GN 136 (Steel / Stainless Steel) → Page 965
- Hinges GN 128 (Steel, for welding) → Page 990
- Stainless Steel-Hinges GN 128.2 (for welding) → Page 991
- Hinges GN 1366 (Steel, for welding) → Page XYZ

How to order

1	Material
2	l_1
3	l_2
4	Type
5	Finish

GN 1362-NI-60-40-A-BL