



EDELSTAHL®
Rostfrei
Inox
Stainless
Steel



d	max. spring load in N ≈	for serrated locking plates GN 187.4 / GN 189 - d ₀	for locking plates GN 187.5 - d ₀
15	40	22	-
18	45	27	27
23	65	32	32
29	90	40	40

Specification

- Stainless Steel AISI 301
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

Stainless Steel-Thrust springs GN 187.2 are placed between serrated locking plates GN 187.4 or GN 189 and locking plates GN 187.5 and ensure that the locking plates separate reliably when removed.

see also...

- *Serrated locking plates (Steel / Stainless Steel) GN 187.4* → Page 824
- *Stainless Steel-Locking plates GN 187.5* → New products

How to order

GN 187.2-18

1 d

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

