



1

2

d_1	d_2	d_3	l_1	l_2
12	M 4	9	40	8
15	M 5	11	50	7
18	M 6	13	64	8
21	M 6	15	72	10
21	M 8	15	72	10
25	M 8	17	90	10
26	M 10	20	100	12
33	M 12	25	124	14

Specification

Handle

- Plastic, Phenolic (PF)
- Operating temperature up to 110 °C
- Black, shiny finish

Spindle

- Steel
- Zinc plated, blue passivated

RoHS

Fixed conical handles GN 203 are suitable for applications where the handle is exposed to low loads. For applications with increased loads we recommend to use cylindrical handles GN 539.

see also...

GN 539 Fixed Cylindrical Handles Page QVX

Technical Information

Plastic Characteristics QVX

How to order

GN 203-15-M5

1 d_1

2 d_2

