



1.1

1.2

1.3

1.4

¹ d ₁	² d ₂	a	b	h ₁	h ₂ ≈	Length l ≈
16	M 8	7	12	12	34	56
20	M 10	9	14	14	42	70
25	M 12	11	18	18	53	87
32	M 16	15	22	22	66	109
40	M 20	18	28	28	84	140

2.1

Specification

- Malleable cast iron —
- fettled
- Contact faces machined
- Stainless Steel-Precision casting **NI**
- AISI CF-8
- fettled
- Contact faces machined
- *Stainless Steel characteristics* → Page 1489
- RoHS



Information

- see also...
- *Clamp nuts with double lever GN 99.7 (Steel, zinc plated)* → Page 369
 - *Stainless Steel-Clamp nuts with double lever GN 99.8* → Page 369

2.2

2.3

On request

- Clamp nuts with double lever GN 206.1 plastic coated

2.4

How to order (Steel)	
¹	d ₁
²	d ₂
GN 206.1-32-M16	

How to order (Stainless Steel)	
¹	d ₁
²	d ₂
³	Material
GN 206.1-20-M10-NI	

