

Inox
Stainless
SteelInch
sizes
available

3 Type

E angled lever

1

2

d ₁	d ₂	d ₃	d ₄	d ₅	h ₁	h ₃	h ₄ ≈	h ₅ Stroke	l ₂ ≈	l ₃ ≈	t min.
21	M 6 M 8	13,5	8	20	33,5	1	59	4	75	70	11
24	M 8 M 10	16	10	25	40	2,5	75	4,5	101	96	14
28	M 10 M 12	19	12	30	48,5	4,5	89	4,5	116	110	17

Specification

- Stainless Steel AISI 303 matte shot-blasted
- Ball knobs DIN 319 Plastic, Duroplast black, shiny finish
- *Stainless Steel characteristics* → Page 1489
- RoHS

On request

- straight lever (90°)

Information

Adjustable tension levers GN 212.5 have proved to be ideal whenever parts have to be clamped in a confined space or a particular lever position is required. The threaded insert is connected with the hub via serrations which can be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever it will automatically re-engage.

see also...

- *Adjustable tension levers GN 212.3 (Steel, blackened)* → Page 346

How to order

GN 212.5-24-M10-E

1	d ₁
2	d ₂
4	Type