



**4 Type**

- L** clamping direction left turn
- R** clamping direction right turn

<b>2</b> $d_1$	<b>3</b> $d_2$ H8 Bore		$d_3$	$l_1 \approx$	$l_2$	$l_3$	$l_4$
35	B 8	B 10	18	15	7	7	3
65	B 12	-	23	20	10	7	5
80	B 16	-	27	24	12	9	6

**Specification**



- Sintered steel **SM**  
black, steam oxidized
- ISO-Fundamental tolerances → Page 1479
- RoHS

How to order

**GN218-SM-35-B10-L**

<b>1</b>	<b>Material</b>
<b>2</b>	$d_1$
<b>3</b>	$d_2$
<b>4</b>	<b>Type</b>

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

