

1.1

1.2

1.3

1.4

1


2

d_1	Length $l \pm 0,25$	d_2	h
8	30	12	26
10	40	15	31

2.1

Specification

3

- **GN 224.1**
Steel
chrome-plated 
Location disks
Zinc die casting, nickel-plated
- **GN 224.5**
Stainless Steel AISI 304
matte shot-blasted
Location disks
Stainless Steel AISI 303
- *Stainless Steel characteristics* → Page 1489
- RoHS

2.2

2.3

2.4

How to order (Steel)	
1 b_1	GN 224.1-8-30-CR
2 l_1	
3 Finish	

How to order (Stainless Steel)	
1 d_1	GN 224.5-10-40
2 Length l	

