



ELESA original design MFH



1.1

1.2

1.3

1.4

1

2

3

d ₁	Length l		d ₂ Bore B	d ₃	h
	Nominal dimension	Actual dimension			
9	30	29,5	B 3,5	12	27
10	40	39,5	B 3,5	15	33,5

2.1

Specification

4

- Plastic
Technopolymer (Polyamide PA)
temperature resistant up to 100 °C
- Color (matte):
 - SW black, RAL 9005
 - OR orange, RAL 2004
 - GR gray, RAL 7035
 - RT red, RAL 3000
 - CL white, RAL 9002, Cleanline
- Plastic characteristics → Page 1483
- RoHS

Information

Finger handles GN 224.3 with bore hole B 3,5 are intended for fixing with self-tapping screws of thread size ST 4,2 such as DIN ISO 7049 pan head tapping screws.

see also...

- Product family Cleanline → Page 17
- Finger handles GN 224.1 → Page 121
- Stainless Steel-Finger handles GN 224.5 → Page 121

2.2

2.3

2.4

How to order

1	d ₁
2	Length l
3	d ₂
4	Color

GN 224.3-10-40-B3,5-SW

