



- 4 Sensitivity**  
30 Angle minutes, bubble move by 2 mm
- 5 Type**
  - A** with smooth reference surface
  - B** with mounting thread

**2**

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>
14	10	M 4	9,5	7,7	5
20	14	M 5	13	13	6
30	21	M 6	15	15	7,5

**Specification**

**1 3**

- Housing
  - Aluminum
    - anodized, natural color  **ALN**
    - anodized, black  **ALS**
- Spirit level element
  - Glass plastic body
  - Filling colorless-transparent **K**
- Casting compound mineral-based
- RoHS

**On request**

- Filling, green-transparent
- Other sensitivities
- Housing in brass or Stainless Steel

**Information**

Bull's eye levels GN 2279 are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

Type A is used if the spirit level is to be used as a tool, e.g. at different measuring points.

The spirit levels are aligned in relation to the reference or contact surface, such that the bubble is located inside the marking ring once the horizontal position of the contact surface is reached.

see also...

- *General information on bull's eye levels and screw-on levels* → Page 243

**How to order**

<b>1</b>	<b>Material / Finish</b>
<b>2</b>	<b>d<sub>1</sub></b>
<b>3</b>	<b>Filling</b>
<b>4</b>	<b>Sensitivity</b>
<b>5</b>	<b>Type</b>

**GN 2279-ALS-20-K-30-A**