



4 Sensitivity
30 Angle minutes,
bubble move by 2 mm

2

d ₁	d ₂	d ₃	d ₄	h ₁	h ₂	t
17	12	13,2	M 3	13	14,7	5
20	14	13	M 3	14,5	17	5
24	16	15	M 3	17	20	5

Specification

- Housing
Aluminum
anodized, natural color **ALN**
anodized, black **ALS**
- Spirit level element
Glass plastic body
Filling
colorless-transparent **K**
- Casting compound
mineral-based
- RoHS

On request

- Filling, green-transparent
- Other sensitivities
- Housing in brass or Stainless Steel

Information

Bull's eye levels GN 2280 are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

The spirit levels do not have a reference surface, and the mounting threads offset by 120° allow the spirit levels to be aligned in relation to the mounting surface. An alignment ball at the bottom surface of the adjustment plate serves as tilting point. Specific tightening torques of the bolts allow to be achieved, so that the bubble is located inside the marking ring once the horizontal alignment is reached.

see also...

- General information on bull's eye levels and screw-on levels → Page 243

How to order

1	Material / Finish
2	d₁
3	Filling
4	Sensitivity

GN 2280-ALS-20-K-30

