



² l ₂	³ s				b ₁	b ₂	d	l ₁	m ₁	m ₂
30	1	1,5	3	5	10,8	6	4	30	18	18
40	1	1,5	3	5	14,5	7,5	5	40	25	25
50	1	1,5	3	5	18	10	6	50	30	30
60	1	1,5	3	5	21,5	12,5	8	60	36	36

Specification

- Stainless Steel **NI**
- AISI 304
- plain, matte tumbled finish **MT**
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

Information

Chamfers, different sheet metal thicknesses, or seals could mean that the mounting surfaces of hinges to frame and door are not on the same level.

Stainless Steel-Spacer plates GN 2370, as accessories of the GN 237 and GN 337 family of hinges, are designed dimensionally so that they ensure the appropriate height compensation during mounting by shimming, either individually or in combination.

see also...

- *Hinges GN 237* → Page 959
- *Hinges GN 237.1 (Plastic)* → Page 964
- *Hinges GN 337 (detachable)* → Page 986

The table includes a number of potential compensation heights which can be accomplished by shimming with one or two spacer plates.

Height compensation	Plate thickness s	Height compensation	Plate thickness s
1	1	4,5	3 + 1,5
1,5	1,5	5	5
2	1 + 1	6	3 + 3
2,5	1 + 1,5	6,5	5 + 1,5
3	3	8	5 + 3
4	3 + 1	10	5 + 5

How to order

¹ ² ³ ⁴
GN 2370-NI-40-5-MT

- 1 Material**
- 2 l₂**
- 3 s**
- 4 Finish**

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

