



- 2** Type
- A** without thread coating
 - PRB** with thread coating (polyamide allround coating)

1

d		h	A/F
GN 252	GN 252.5		
M 12 x 1,5	M 12 x 1,5	10	6
M 16 x 1,5	M 16 x 1,5	10	8
M 20 x 1,5	M 20 x 1,5	12	10
M 24 x 1,5	M 24 x 1,5	12	14
M 27 x 1,5	M 27 x 1,5	12	14
M 30 x 1,5	-	12	17
M 33 x 1,5	-	12	17

Specification

- **GN 252**
Steel
- Tensile strength class 5.8
- blackened
- **GN 252.5**
Stainless Steel AISI 303
- *Strength values of screws* → Page 1481
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

Information

The thread locking PRB (polyamide allround coating) is a clamping lock which prevents the locking screw from being inadvertently being loosened and becoming detached.

see also...

- *Threaded plugs GN 749 (with sealing ring rubber)* → Page 1115
- *Threaded plugs DIN 906 (with conical thread)* → Page 1116
- *Threaded plugs DIN 908* → Page 1117
- *More information to thread lockings* → Page 1495 ff.

How to order (Steel)	1 d
GN 252-M24x1,5-A	2 Type

How to order (Stainless Steel)	1 d
GN 252.5-M16x1,5-PRB	2 Type

