



2	Type
MCR	matte chrome plated
MCRS	matte chrome plated, standard scale 0...90, 100 graduations, acc. scale scheme d <sub>i</sub> /100 A RA 0-10 20...90/10

1

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub> H7	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	Scaling set consists of: 1 Scale ring GN 264	
						2 Collar bushings	3 Flat springs
30	27	24	33	16	23,7	GN 268-24-K...	GN 374-0,3-10
40	36	32	43	16	23,7	GN 268-32-K...	GN 374-0,4-10
60	55	50	63	16	25,7	GN 268-50-K...	GN 374-0,6-10
80	75	68	83	16	25,7	GN 268-68-K...	GN 374-0,8-10

**Specification**

- Steel  
Scale lug d<sub>1</sub> fine turned  
- blank (standard version)  
- matte chrome plated  
- matte chrome plated with standard scale
- Scale  
engraved with laser precision, black
- ISO-Fundamental tolerances → Page 1479
- RoHS

2

**Information**

Besides the standard scale (Type MCRS) the scale rings can be supplied with any type of graduation. It is suggested to use the matte chrome plated version (MCR) so that a nice discrepancy in color is given.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale rings on the order sheet „How to order Graduations“ → Page 252.

see also...

- Collar bushing GN 268 → Page 256
- Flat springs GN 374 → Page 256
- Scale rings GN 164 (with and without scale) → Page 253

**On request**

- special graduations  
see „How to order Graduations“ → Page 252

How to order (Scale ring without scale)	1	d <sub>1</sub>
<b>GN 264-80</b>		

How to order (Scale ring with scale)	1	d <sub>1</sub>
<b>GN 264-40-MCRS</b>	2	Type