



b Swivel width	d ₁	d ₂	d ₃	Length l	m ₁	m ₂	t ₁	t ₂	s	x ₁	x ₂	y
25	6,5	5,5	36,5	24	25	12,5	7	10	50	38	35	35

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Plain finish, matte shot-blasted ○ **BL**
 - Stainless steel AISI CF-8 **NI**
 - Matte shot-blasted
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Swivel clamp connectors GN 271 can be combined with swivel clamp connectors GN 273, GN 275 or GN 277 to swivel clamp connector joints.

Swivel clamp connector GN 271 can also be mounted to **profile systems**.

see also...

- Product Family Standard Parts for Profile Systems → Page 18
- Swivel Clamp Connector Joints GN 281
(Connection of GN 271 with GN 275) → Page 1763
- Sensor Holders GN 271.4 → Page 1776

How to order (Aluminum)	1	b
	2	Finish
GN 271-25-SW		
How to order (Stainless steel)	1	b
	2	Material
GN 271-25-NI		