



- 3 Identification no.**
- 2 with 3 Stainless Steel-Clamping screws DIN 912**

<b>1</b> <b>d<sub>1</sub></b> Bore B	<b>2</b> <b>d<sub>2</sub></b> Bore B	<b>b</b> Swivel width	<b>d<sub>3</sub></b> Clamping thread	<b>k<sub>1</sub></b>	<b>k<sub>2</sub></b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>l<sub>3</sub></b>	<b>m<sub>1</sub></b>	<b>m<sub>2</sub></b>	Clamping kit for d <sub>3</sub>
B 12	B 12	25	M 6	25	25	100	34,5	25	29,5	48,5	GN 911-M6-22
B 14	B 14	25	M 6	25	25	100	34,5	25	29,5	48,5	GN 911-M6-22
B 16	B 16	25	M 6	25	25	100	34,5	25	29,5	48,5	GN 911-M6-22
B 18	B 18	25	M 6	25	25	100	34,5	25	29,5	48,5	GN 911-M6-22

**Specification**

- Aluminum
  - plastic coated  
black, RAL 9005, textured finish **● SW**
  - blank **○ BL**  
matte shot-blasted
- Clamping bores mechanically machined
- Socket cap screws DIN 912  
Stainless Steel AISI 304
- Hexagon nuts DIN 985  
Stainless Steel AISI 304
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

**Accessory**

- Clamping kits GN 911 → Page 1242



**Information**

GN 287 swivel clamp connector joints are an assembly of swivel clamp connectors GN 275 and GN 277.

Since the swivel clamp connectors have an identical swivel width “b”, all bores “d<sub>1</sub> / d<sub>2</sub>” can be combined as required.

The clamping bores are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462 respectively.

The standard version of the clamping screws are socket cap screws with hexagonal socket DIN 912. They can be replaced by clamping kits GN 911 (see table of dimensions).

see also...

- *Construction tubes GN 990* → Page 1277
- *Retaining rods / Retaining tubes GN 480.1* → Page 1276
- *Swivel clamp connectors GN 275* → Page 1224
- *Swivel clamp connectors GN 277* → Page 1226

How to order

<b>1</b>	<b>d<sub>1</sub></b>
<b>2</b>	<b>d<sub>2</sub></b>
<b>3</b>	<b>Identification no.</b>
<b>4</b>	<b>Finish</b>

**GN 287-B12-B12-2-SW**