



- 3 Type**
- S stepless adjustment
- 4 Identification no.**
- 2 with 5 Stainless Steel-Clamping screws DIN 912



1 d1 Bore B	1 s1 Square V	2 d2 Bore B	2 s2 Square V	b Swivel width	d3 Clamping thread	d4 Clamping thread	k	l1	l2	m	Clamping kit	
											for d3	for d4
B 40	V 40	B 40	V 40	65	M 10	M 10	76	268	70	85	GN 911-M10-55	GN 911-M10-63
B 42	-	B 42	-	65	M 10	M 10	76	268	70	85	GN 911-M10-55	GN 911-M10-63
B 45	V 45	B 45	V 45	65	M 10	M 10	76	268	70	85	GN 911-M10-55	GN 911-M10-63
B 48	-	B 48	-	65	M 10	M 10	76	268	70	85	GN 911-M10-55	GN 911-M10-63
B 50	V 50	B 50	V 50	65	M 10	M 10	76	268	70	85	GN 911-M10-55	GN 911-M10-63

Specification

- Aluminum
 - plastic coated
 - black, RAL 9005, textured finish ● **SW**
 - blank ○ **BL**
 - matte shot-blasted
- Clamping bore not machined
- Socket cap screws DIN 912
Stainless Steel AISI 304
- Hexagon nuts DIN 985
Stainless Steel AISI 304
- Stainless Steel characteristics → Page 1489
- RoHS

Accessory

- Clamping kits GN 911 → Page 1242

Information

GN 289 swivel clamp connector joints are an assembly of two GN 279 swivel clamp connectors.

The clamping bores of GN 289 swivel clamp connector joints are not machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462 respectively.

The swivel clamp connectors have an identical swivel width "b", so that all bores „d₁ / s₁“ and „d₂ / s₂“ can be combined as required.

The standard version of the clamping screws are socket cap screws with hexagonal socket DIN 912. They can be replaced by clamping kits GN 911 (see table of dimensions).

see also...

- Construction tubes GN 990 → Page 1277
- Swivel clamp connectors GN 279 → Page 1228

How to order

GN 289-B40-V40-S-2-BL

1	d ₁ (s ₁)
2	s ₂ (d ₂)
3	Type
4	Identification no.
5	Finish