



Inch sizes available

1 l_1	2 d_1 Thread			2 d_2 H7 Bore		d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
22	M 3	M 4	M 5	B 4	B 5	8	10,5	18,5	2	16,5	3	5
30	M 3	-	-	-	-	10	13	24,5	4	22	3,5	7
30	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	22	3,5	9
45	M 4	M 5	M 6	B 5	B 6	10	13	24,5	4	22	3,5	9
63	M 6	M 8	-	B 8	-	13,5	17,5	31	6,5	28,5	4	11
78	M 8	M 10	M 12	B 8	B 10	16	21	36	8	34	4	14

Specification

- Handle
Zinc die casting
- Plastic coated
black, RAL 9005, textured finish **● SW**
orange, RAL 2004, textured finish **● OS**
red, RAL 3000, textured finish **● RS**
silver, RAL 9006, textured finish **● SR**
- Bushing and retaining screw
Steel, blackened
- ISO-Fundamental tolerances → Page 1479
- RoHS

Information

Adjustable hand levers GN 302 have a straight lever, not inclined, being parallel to the clamping space.

Adjustable hand levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The centre insert is connected to the lever via serrations which can easily be disengaged.

Pulling the lever, disengages the serrations and allowing it to be swivelled to the ideal clamping position. On releasing the lever the serrations automatically re-engage.

see also...

- Flat adjustable hand levers GN 302.1 (bushing Stainless Steel) → Page XYZ
- Adjustable hand levers GN 300 (bushing steel) → Page 318
- Adjustable hand levers GN 300.1 (bushing Stainless Steel) → Page 322

<p>How to order</p> <p>GN 302-45-M4-SR</p>	1 l_1
	2 d_1 (d_2)
	3 Color