



**3 Type**

- A** With threaded stud
- B** With internal thread

<b>1</b> $d_1$	<b>2</b> $d_2$	$d_3$	$l_1$	$l_2 \pm 1$	$l_3 \pm 1$	A/F	t min.
25	M 6	10	11	37,5	15	8	10
32	M 8	13	13	48	19	10	12
40	M 10	16	14	61	24	14	16
50	M 12	20	21	78	31	17	16

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 110 °C  
- Black, shiny finish
- Spindle  
Stainless Steel AISI 303  
Matte shot-blasted
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**On request**

- With inch threads

**Information**

Revolving ball knobs GN 319.5 are in general used where a „pulling action“ is involved such as on vertically positioned handwheels.

see also...

- *Revolving Softline Mushroom Shaped Handles GN 597.1* → Page 45

**How to order**

**GN319.5-25-M6-B**

<b>1</b>	$d_1$
<b>2</b>	$d_2$
<b>3</b>	Type

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

