



4 Form (Fußteller)

A1 Stahl, verzinkt
Gummi eingelegt, schwarz

1		2		3		3												
d ₁	d ₂	l ₁		Version S / SK						Version U / UK				l ₇	h ₁	d ₄	l ₈	l ₉
50	M 8	40	50	63	-	-	-	-	-	-	-	40	18	13	25	45		
50	M 10	50	60	80	100	-	-	-	-	-	-	43	18	13	25	45		
50	M 12	60	80	100	125	-	-	-	-	-	-	47	18	13	25	45		
50	M 16	-	-	-	-	75	100	125	150	200	52	18	13	25	45			
60	M 8	40	50	63	-	-	-	-	-	-	41	19	13	25	50			
60	M 10	50	60	80	100	-	-	-	-	-	44	19	13	25	50			
60	M 12	60	80	100	125	-	-	-	-	-	48	19	13	25	50			
60	M 16	-	-	-	-	75	100	125	150	200	53	19	13	25	50			
80	M 8	40	50	63	-	-	-	-	-	-	42	20	13	30	70			
80	M 10	50	60	80	100	-	-	-	-	-	45	20	13	30	70			
80	M 12	60	80	100	125	-	-	-	-	-	49	20	13	30	70			
80	M 16	-	-	-	-	75	100	125	150	200	54	20	13	30	70			
80	M 20	-	-	-	-	75	100	125	150	200	62	20	13	30	70			
80	M 24	-	-	-	-	100	125	150	200	-	-	20	13	30	70			
100	M 8	40	50	63	-	-	-	-	-	-	43	21	13	30	80			
100	M 10	50	60	80	100	-	-	-	-	-	46	21	13	30	80			
100	M 12	60	80	100	125	-	-	-	-	-	50	21	13	30	80			
100	M 16	-	-	-	-	75	100	125	150	200	55	21	13	30	80			
100	M 20	-	-	-	-	75	100	125	150	200	63	21	13	30	80			
100	M 24	-	-	-	-	100	125	150	200	-	-	21	13	30	80			

Specification

- Base plate / lug, sheet metal
Steel, zinc plated, blue passivated
- Threaded stem
Steel, zinc plated, blue passivated
- Hexagon nut ISO 4032
Steel, zinc plated, blue passivated
- Rubber underlay, inlaid
black, Perbunan® (NBR)
80±5 Shore A
- Elastomer characteristics → Page 1483
- Load rating information → Page 1471
- RoHS

Versions of threaded stem

<p>S without nut SK with nut</p>	<p>U without nut UK with nut</p>	<p>X with female thread</p>
<p>External hexagon at the bottom at d_2 M 8, M 10, M 12</p>	<p>Hexagon socket at the top Wrench flat at the bottom at d_2 M 16, M 20, M 24</p>	<p>External hexagon with female thread at d_2 M 8, M 10, M 12, M 16, M 20</p>

d_1	d_2	h_3	h_4	A/F ₁	A/F ₂	A/F ₃	A/F ₇	t
50	M 8	26	-	17	-	-	14	8
50	M 10	26	-	17	-	-	14	10
50	M 12	26	-	17	-	-	17	12
50	M 16	-	32	-	12	8	22	16
60	M 8	27	-	17	-	-	14	8
60	M 10	27	-	17	-	-	14	10
60	M 12	27	-	17	-	-	17	12
60	M 16	-	33	-	12	8	22	16
80	M 8	28	-	17	-	-	14	8
80	M 10	28	-	17	-	-	14	10
80	M 12	28	-	17	-	-	17	12
80	M 16	-	34	-	12	8	22	16
80	M 20	-	35	-	15	10	27	20
80	M 24	-	38	-	19	12	-	-
100	M 8	29	-	17	-	-	14	8
100	M 10	29	-	17	-	-	14	10
100	M 12	29	-	17	-	-	17	12
100	M 16	-	35	-	12	8	22	16
100	M 20	-	36	-	15	10	27	20
100	M 24	-	39	-	19	12	-	-

Information

Levelling feet GN 32 will be delivered mounted and are not removable.

see also...

- *Stainless Steel-Levelling feet GN 33 (with fixing lug) → Page 1050*
- *Levelling feet GN 30 (Steel, zinc plated, without fixing lug) → Page 1044*

How to order		1	d_1
		2	d_2
		3	l_1 (l_7)
		4	Type (Base plate)
		5	Version (Stem)

GN 32-100-M20-150-A1-U