



Socket button head screw **3 Type**

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side (only for $d_1 = 28$)

d_1	Length $l \pm 0,25$								d_2	d_3	b_1	b_2	h_1	h_2	t min.
	180	200	250	300	350	400	-	600							
20	180	200	250	300	350	400	-	M 6	-	24	12	42	54	12	
28	200	250	300	350	400	500	600	M 8	M 6	25	14	50	66	15	
30	200	300	350	400	500	600	1000	M 8	-	27	17	51	68	15	

Specification

- Handle tube
Aluminum (wall thickness 1,5)
- Handle legs
Zinc die casting
- Tube **SW**
plastic coated
black, RAL 9005, textured finish
Handle legs plastic coated
black, RAL 9005, textured finish
- Tube **EL**
anodized, natural color
Handle legs plastic coated
black, RAL 9005, textured finish
- Tube **ES**
anodized, natural color
Handle legs plastic coated
silver, RAL 9006, textured finish
- Cover
Plastic, light gray
- Type B
 - Socket button head screws
ISO 7380-M6-20
 - Hexagon nuts ISO 4032-M6
 - Washers DIN 125
- Steel, zinc plated, blue passivated
- Load rating information → Page 1450
- RoHS

Information

The handle tube of the GN 333.1 tubular handles can be screwed to the handle bases without further machining or processing, allowing **special lengths** to be realised easily.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles $\varnothing 28$ (type A) are available under GN 333.9 → Page 135.

For type B, socket button head screws, hexagon nuts and washers are included parts of the order.

see also...

- Product family Standard Parts for profile systems → Page 20
- Tubular handles GN 333 (angled) → Page 136
- Stainless Steel-Tubular handles GN 333.5 → Page 134
- Tubular handles GN 331 (with power switching function) → Page 132
- Assembly sets for profile systems 30 / 40 GN 965 → Page 1428
- Assembly sets for profile systems 30 / 40 / 45 GN 968 → Page 1438

How to order	1 d_1
	2 Length l
	3 Type
	4 Finish

1 2 3 4
GN 333.1-28-400-B-SW