



3.1

3.2

3.3

3.4

3.5

<b>1</b> $d_1$	<b>2</b> $d_2$		<b>3</b> $h_1$	$b$	$d_3$	$d_4$ for screw	$h_2$	$m$
45	M 6	M 8	16	25	15	M 6	6	30
60	M 10	M 12	24	30	21,5	M 8	6	40

3.6

**Specification**

- Steel fine casting
  - zinc plated, blue passivated
  - zinc plated and plastic coated black, RAL 9005, textured finish
  - RoHS
- ZB** **SW**

**4 Information**

Threaded flanges GN 3490 are used in connection with T-slot profile systems and allow elements to be assembled on or underneath the profiles, e.g. levelling feet.

Depending on the threaded flange, thread size and thread depth dimensions that are available can exceed the dimensions of the profile groove.

see also...

- Assembly sets for profile systems 30 / 40 GN 965 → Page 1428
- Assembly sets for profile systems 30 / 40 / 45 GN 968 → Page 1438

3.7

3.8

3.9

How to order	<b>1</b> $d_1$
	<b>2</b> $d_2$
	<b>3</b> $h_1$
	<b>4</b> Finish

**GN 3490-45-M8-16-SW**

