



elesa

ELESA Original design M.479

2 Type

- A** Mounting from the back
- B** Mounting from the operator's side

1

$l_1 \pm 0,5$	d_1	d_2	b	h_1	h_2	l_2	l_3	s	t_1	t_2
132	M 8	8,5	23	52,5	13	173	113	9	12	8,5

Specification

- Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black-gray, shiny finish
similar RAL 7021
- Bushing (type A) brass
- Color of the cover cap (matte):
 - **DSG**
black-gray, RAL 7021
 - **DOR**
orange, RAL 2004
 - **DGR**
gray, RAL 7035
 - **DGB**
yellow, RAL 1021
 - **DBL**
blue, RAL 5024
 - **DRT**
red, RAL 3000
- *Strength properties* → Page XYZ
- *Plastic characteristics* → Page 1483
- RoHS

3

Information

The cover caps of arch handles GN 365 for type A are mounted on the handle, but supplied loose for type B.

How to order

GN365-132-A-DSG

1	l_1
2	Type
3	Color of the cover cap