



1	2	3	4						
b	d	$l_1 \pm 0,5$	a	h	l_2	l_3	l_4	t min.	
36	M 6 M 8	200	24	57	236	164	290	15	
36	M 6 M 8	250	24	57	286	214	340	15	
36	M 6 M 8	300	24	57	336	264	390	15	
36	M 6 M 8	400	24	57	436	364	490	15	
36	M 6 M 8	500	24	57	536	464	590	15	
36	M 6 M 8	600	24	57	636	564	690	15	

Specification

- Handle tube
Aluminum
- Handle legs / covers
plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 100 °C
- Tube **SW**
plastic coated
black, RAL 9005, textured finish
Handle legs / covers
black, matte
- Tube anodized, natural color **ELS**
Handle legs / covers
black, matte
- Tube anodized, natural color **ELG**
Handle legs / covers
light gray, matte
- Bushing
Steel, zinc plated
- Load rating information → Page 1451
- Plastic characteristics → Page 1483
- RoHS



Information

Characteristic for the design of the GN 366 oval handles: Tube and handle shank are made in the same elliptical profile.

see also...

- Oval tubular handles GN 334 (Mounting from the back) → Page 142

How to order

GN366-36-M8-400-ELS

1	b
2	d
3	l_1
4	Finish