



Steel

d ₁	d ₂	d ₃	d ₄	h	k	Length l
M 4	9	12	19	14	8	9
M 5	9	12	19	14	8	9
M 6	12	14	24	16,5	9,5	10,5
M 8	14	16	30	19,5	11	11,5
M 10	16	18	36	22,5	12,5	14



Stainless Steel

d ₁	d ₂	d ₃	d ₄	h	k	Length l
M 5	9	12	19	14	8	9
M 6	12	14	24	16,5	9,5	10,5
M 8	14	16	30	19,5	11	11,5

Specification

- Plastic
Technopolymer (Polyamide PA)
black, shiny finish
- Bushing
 - Steel zinc plated, blue passivated —
 - Stainless Steel AISI 303 **NI**
- *Stainless Steel characteristics* → Page 1489
- *Plastic characteristics* → Page 1483
- RoHS

Information

see also...

- *Knurled nuts GN 420 with loss protection GN 111.7* → Page 1426

How to order (Steel)

GN 420-M8

1 d₁

How to order (Stainless Steel)

GN 420-M6-NI

1 d₁

2 Material