



d₁	Length l ±0,5							d₂	d₃	h	r	t min.
6	32	45	55*	64	88*	-	-	M 3	9	26	7	7
8	55*	64	88*	96	100	120*	128	M 4	12	35	10	8
10	88*	100	120*	180*	200	235*	-	M 5	15	43	12	12
12	125	160	200	250	-	-	-	M 6	-	51	14	12
16	160	200	250	300	-	-	-	M 6	-	59	18	12

* suitable for 19" rack and enclosure layout

Specification

- Steel
 - plastic coated
 - black, RAL 9005, textured finish ● **SW**
 - chrome-plated ● **CR**
 - blackened ● **BT**
- Location disks
 - Zinc die casting, nickel plated
- Load rating information → Page 1452
- RoHS

Information

Cabinet U-handles GN 425 are manufactured from a bent steel profile. Cabinet „U” handles with $\varnothing d_1 = 6, 8$ and 10 are delivered with two location disks to ensure proper contact of the handle even in the case of large connecting holes. The disks are loosely enclosed.

Due to the manufacturing process, **special designs** can be supplied even in relatively small quantities.

The Stainless Steel version is preferred over the chrome-plated version for outdoor applications.

see also...

- Cabinet U-handles GN 425.1 (Steel, angled) → Page 106

How to order

GN 425-10-120-CR

1	d₁
2	Length l
3	Finish