



ROSTFREI®  
Inox  
Stainless  
Steel

d <sub>1</sub>	Length l ±0,25			d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	r	t min.
	NI	A4	AL						
8	-	8	55* 64 88* 96 100	M 4	12	40	30	9	8
10	10	10	88* 100 120* 180* 200	M 5	15	47	35	11	12
12	-	12	125 160 200 250 -	M 6	-	60	44	12	12

\* suitable for 19" rack and enclosure layout

Specification

- Stainless Steel **NI**
  - AISI 303 (A1) for d<sub>1</sub> = 8, 10
  - AISI 304 (A2) for d<sub>1</sub> = 12
  - matte shot-blasted **GS**
  - electropolished **EP**
- Stainless Steel **A4**
  - AISI 316L
  - matte shot-blasted **GS**
- Aluminum **AL**
  - plastic coated
  - black, RAL 9005, textured finish **● SW**
  - silver, RAL 9006, textured finish **● SR**
  - red, RAL 3000, textured finish **● RS**
  - anodized, natural color **● EL**
- Location disks
  - Zinc die casting, nickel plated (for AL)
  - Stainless Steel, AISI 303 (for NI)
  - Stainless Steel, AISI 316L (for A4)
- Load rating information → Page 1453
- Stainless Steel characteristics → Page 1489
- RoHS

Information

Cabinet U-handles GN 425.1 are manufactured from a bent Stainless Steel or aluminum profile. Cabinet „U“ handles with Ø d<sub>1</sub> = 8 and 10 are delivered with two location disks to ensure proper contact of the handle even in the case of large connecting holes. The disks are loosely enclosed.

Due to the manufacturing process, **special designs** can be supplied even in relatively small quantities.

The Stainless Steel version is preferred over the chrome-plated version in steel for outdoor applications.

see also...

- Cabinet U-handles GN 425 (Aluminum / Stainless Steel, not angled) → Page 103

How to order (Stainless Steel)	
1	Material
2	d <sub>1</sub>
3	Length l
4	Finish

How to order (Aluminum)	
1	Material
2	d <sub>1</sub>
3	Length l
4	Finish

