



ELESA Original design MMT.

1

2

d ₁	l ₁ ±0,5	l ₂	b	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄	t min.
10	120	94	16	M 5	18	53	43	8	24	12
10	180	94	16	M 5	18	56	43	8	24	12

Specification

- Steel
matte chrome-plated
- Plastic handle
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 150 °C
- black, matte
- *Plastic characteristics* → Page 1483
- RoHS

Information

Cabinet U-handles GN 425.7 made of steel feature a plastic grip which, owing to its insulating properties, allows it to be used under high surface temperatures.

The above temperature distribution curve has been measured at a surface temperature of 200 °C and a room temperature of 23 °C.

see also...

- *Cabinet U-handles GN 425 (Steel)* → Page 103

How to order

GN 425.7-10-120

1 d₁

2 l₁

