



d ₁	Length l ±0,25	Finish WSA / SMA	d ₂	h	r	t min.
20	250	250	M 8	68	22	15
20	300	300	M 8	68	22	15
20	350	-	M 8	68	22	15
28	250	250	M 10	78	32	15
28	300	300	M 10	78	32	15
28	350	-	M 10	78	32	15
28	400	400	M 10	78	32	15

Specification

- Aluminum **AL**
 - d₁ = 20: Solid material
 - d₁ = 28: Tube-Ø 28 x 4
 - plastic coated
 - black, RAL 9005, textured finish ● **SW**
 - black, RAL 9005, antibacterial ● **SMA**
 - silver, RAL 9006, textured finish ● **SR**
 - white, RAL 9016, antibacterial ○ **WSA**
 - blank ○ **BL**
 - tumbled
- Threaded bushing Aluminum
- Load rating information → Page 1454
- RoHS

Information

GN 426 cabinet U-handles are manufactured from a bent aluminum profile and have excellent stability and ergonomic design. Due to the manufacturing process, **special designs** can be supplied even in relatively small quantities.

In addition to the standard surfaces, these cabinet U-handles are also available with a functional coating.

The **WSA / SMA** versions have a powder coating based on zinc molybdate, which gives it antibacterial properties. The principle of action, which is activated by the presence of moisture, demonstrably reduces the growth of bacteria within 24 hours, so that contaminated surfaces ultimately have less than 0.2% of the original number of microbes.

Standard elements with antibacterial plastic coating are primarily used in the health care sector and in public buildings, such as airports, train stations, stadiums, etc.

see also...

- Cabinet U-handles GN 428 (Aluminum) → Page 117

How to order

1 2 3 4
GN 426-AL-28-300-SW

1	Material
2	d ₁
3	Length l
4	Finish