



<b>1</b> b	<b>2</b> Length l ±0,25	a	h	r
12	55*	8	40	8
12	88*	8	40	8
12	100	8	40	8
12	120*	8	40	8
12	180*	8	40	8
12	200	8	40	8
12	235*	8	40	8

\* suitable for 19" rack and enclosure layout

**Specification**

- **GN 427**  
Aluminum  
- plastic coated  
black, RAL 9005, textured finish ● **SW**  
silver, RAL 9006, textured finish ○ **SR**  
- anodized, natural color ○ **EL**
- **GN 427.5**  
Stainless Steel AISI 304  
matte shot-blasted
- Load rating information → Page 1454
- Stainless Steel characteristics → Page 1489
- RoHS



**Information**

Cabinet U-handles GN 427 / GN 427.5 are manufactured from a bent aluminum / Stainless Steel profile.

Due to the manufacturing process, **special designs** can be supplied even in relatively small quantities.

see also...

- Cabinet U-handles GN 425 (Aluminum / Stainless Steel) → Page 103

How to order (Aluminum)	<b>1</b> b
	<b>2</b> Length l
	<b>3</b> Finish
<b>GN 427-12-120-EL</b>	

How to order (Stainless Steel)	<b>1</b> b
	<b>2</b> Length l
<b>GN 427.5-12-180</b>	