



d <sub>1</sub>	Length l ±0,5		d <sub>2</sub>	d <sub>3</sub>	h	r	t min.
12	125	160	M 5	12,8	51	14	12
16	160	200	M 6	16,8	59	18	12

Specification

- Stainless Steel
  - AISI 316 L A4
  - matte (Ra < 0.8 µm) MT
  - polished (Ra < 0.8 µm) PL
- Sealing rings
  - hydrogenated acrylonitrile butadiene rubber (H-NBR)
  - blue
  - temperature resistant -25 °C to +150 °C
  - Hardness 85±5 Shore A
  - FDA compliant
- *Elastomer characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

GN 429 Stainless Steel-Cabinet U-handles are intended for use in hygiene areas. The sealed mounting surfaces enable fastening without dead spaces. The high quality finish prevents adherence of dirt and facilitates cleaning.

Due to the manufacturing process, **special designs** can be supplied even in relatively small quantities.

see also...

- Product family *Hygienic Design* → Page 16 / 18
- Sealing rings *Hygienic Design* GN 7600 → Page 881

How to order		1	Material
		2	d <sub>1</sub>
		3	Length l
		4	Finish
GN 429-A4-12-160-MT			