



Inch sizes available

**3 Identification no.**

- 1 without vent hole
- 2 with vent hole

**1** **2**

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub> Vent hole	d <sub>4</sub>	l <sub>1</sub> ±0,5	l <sub>2</sub>	l <sub>3</sub>	s	t min.
22	G 3/8	M 16 x 1,5	2	M 5	26	8	15	5	8
26	G 1/2	M 20 x 1,5	2	M 5	27,5	8,5	16	5	8
32	G 3/4	M 26 x 1,5	2	M 5	29	9	17	6	8
40	G 1	-	2	M 5	32,5	11	18	7	8

**Specification**

- Aluminum
  - plastic coated
  - black, RAL 9005, textured finish
  - blank, tumbled
- **GN 441**
  - temperature resistant up to 100 °C
  - Seal rubber NBR (Perbunan®)
- **GN 442**
  - temperature resistant up to 200 °C
  - Seal rubber FPM (Viton®)
  - Identification by not black finish of the seal
- *Elastomer characteristics* → Page 1483
- **RoHS**

**4**

**Information**

- Threaded plugs GN 441 / GN 442 with the external diameter d<sub>1</sub> match the screw-in holes for DIN 3852 pipe bolt connections.
- The sealing ring is embedded in a radial recess on the plane side, which makes the seal captive and cannot be squeezed out during tightening.
- see also...
- *Threaded plugs GN 741 / GN 742 (with external hexagon)* → Page 1114
  - *Plugs GN 548.1 (Plastic)* → Page 1120

**On request**

- Version with dipstick

How to order (100 °C)

**1** **2** **3** **4**

**GN 441-22-M16x1,5-1-BL**

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Identification no.
4	Finish

How to order (200 °C)

**1** **2** **3** **4**

**GN 442-40-G1-1-SW**

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Identification no.
4	Finish

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

