



1

2

d ₁	d ₂ H7	d ₃ -0,3	d ₄	Length l	s -0,15	t min.
M 6	8	18	8,5	19	9	9
M 8	10	20	11	24	12	11
M 10	12	25	13,5	28	14	14
M 12	16	32	16	34	17	16

Specification

- Steel
- Tensile strength class 5
- blackened
- *ISO-Fundamental tolerances* → Page 1479
- *Strength values of nuts* → Page 1481
- RoHS

Information

In combination with grub screws (i.e. DIN 913 or DIN 6379) swing nuts GN 444.2 can be used together as swing bolts in varying lengths.

In addition, used with a cap screw DIN 912, a swivelling clamping screw can be produced.

Dimensions d₂, d₃ and s are identical to DIN 444.

For stocking purposes cylinder head shoulder bolts GN 732 can be used for the sizes M8, M10 and M12.

see also...

- *Cylinder head shoulder bolts GN 732* → Page 787
- *Joint pieces GN 752 (for Fork joints)* → Page 1165

How to order

GN 444.2-M10-12

1 d₁

2 d₂