


GN 449.1 Spring-bolt door latches

Plastic, adjustable, with cover



ELESA original design BMST



2 Type

- A** Snap lock, without interlock, without finger handle
- B** Snap lock, with interlock, with finger handle

1

b	Holding force F in N (Type A with 1 mm distance)
57	100

Specification

- Plastic (Polyamide PA)
 - glass-fiber reinforced
 - temperature resistant up to 80 °C
 - black, matte
 - gray, matte
- Cover
Plastic (Polybutylene terephthalate PBT)
- Bearing plate
Steel, blackened
- Spring
Stainless Steel
- Plastic characteristics → Page 1483
- RoHS compliant

- SW
- LG

3

Information

GN 449.1 spring-bolt door latches can be mounted on shaped parts and make it easier to hold swinging doors.

The slots allow the spring-bolt door latches to be mounted on shaped parts with different cross-sections. In addition, the distance of 1 mm between the individual elements, which is needed for the latches to work, can be easily adjusted.

In the design with finger handle (Type B), the door is held shut with form-locking effect. The door is opened by unlocking the finger handle. This handle often saves using the extra operating handle at the door.

GN 449.1 spring-bolt door latches will be delivered unmounted.

see also...

- Assembly sets for profile systems 30 / 40 GN 965 → Page 1428
- Assembly sets for profile systems 30 / 40 / 45 GN 968 → Page 1438

How to order

GN 449.1-57-B-SW

- 1 **b**
- 2 **Type**
- 3 **Color**

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

