



1

d ₁	d ₂	d ₃	h	k
M 3	12	6	3	2,5
M 4	16	8	4	3,5
M 5	20	10	5	4
M 6	24	12	6	5
M 8	30	16	8	6
M 10	36	20	10	8
M 12	40	22	12	10

Specification

- Steel
 - Tensile strength class 5
 - visible face fine turned
 - blackened
 - zinc plated, blue passivated
 - Stainless Steel AISI 303
 - AISI 303
 - matte shot-blasted
- [Strength values of nuts → Page 1481](#)
[Stainless Steel characteristics → Page 1489](#)
- RoHS

2

Information

The official standard sheet also provides for the sizes M1 / M1,2 / M1,4 / M1,6 / M2 and M2,5, on the other hand lack the size M12.

see also...

- [Stainless Steel-Knurled nuts GN 536 → Page 452](#)
- [Stainless Steel-Knurled nuts DIN 6303 → Page 455](#)
- [Knurled nuts DIN 466 → Page 456](#)
- [Knurled nuts DIN 466 with loss protection GN 111.7 → Page 1426](#)

How to order (Steel, blackened)	1	d ₁
DIN 467-M3		

How to order (Steel, zinc plated)	1	d ₁
DIN 467-M12-ZB	2	Finish

How to order (Stainless Steel)	1	d ₁
DIN 467-M8-NI	2	Material