



1

d ₁	d ₂	d ₃	h	k
M 3	12	6	3	2,5
M 4	16	8	4	3,5
M 5	20	10	5	4
M 6	24	12	6	5
M 8	30	16	8	6
M 10	36	20	10	8
M 12	40	22	12	10

Specification

2

- Steel
 - Tensile strength class 5
 - visible face fine turned
 - blackened —
 - zinc plated, blue passivated **ZB**
- Stainless Steel AISI 303 **NI**
 - AISI 303
 - matte shot-blasted
- *Strength values of nuts* → Page 1481
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

Flat knurled nuts DIN 467 are suitable for universal use and can be tightened and loosened easily without tools. A nut with thread M12 is also available in addition to the types defined in the DIN standard.

see also...

- *Stainless Steel-Knurled nuts GN 536* → Page 452
- *Stainless Steel-Knurled nuts DIN 6303* → Page 455
- *Knurled nuts DIN 466* → Page 456
- *Knurled nuts DIN 466 with loss protection GN 111.7* → Page 1426

How to order (Steel, blackened)	1	d ₁
DIN 467-M3		

How to order (Steel, zinc plated)	1	d ₁
DIN 467-M12-ZB	2	Finish

How to order (Stainless Steel)	1	d ₁
DIN 467-M8-NI	2	Material