



Length l	d <sub>1</sub> H7 Bore		s H11 Square		d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> ≈	Ø Handle GN 598
	GN 471	GN 471.1	GN 471	GN 471.1							
50	-	B 8	-	V 8	16	18	18	10	10	28,5	14
64	-	B 10	-	V 10	19	22	20	11	12	42,5	18
80	B 10	B 10	V 10	V 10	23	26	24	14	14	52,5	21
100	B 12	B 12	V 12	V 12	27	30	28	17	15	67,5	23
125	B 14	-	V 14	-	32	35	34	22	18	82,5	26
160	B 17	-	V 17	-	35	39	38	26	18	82,5	26

## Specification

- Body
  - **GN 471:** Aluminum
  - **GN 471.1:** Zinc die casting
  - Plastic coated  
black, textured finish
  - Face of the hub machined
- Revolving handles GN 598
  - Plastic, Technopolymer  
black, matte
  - Spindle steel  
zinc plated, blue passivated
- Square DIN 79 → Page 1424
- Cross holes GN 110 → Page 1422
- ISO-Fundamental tolerances → Page 1479
- RoHS

How to order (Aluminum)	
1	Length l
2	d <sub>1</sub> (s)

**GN 471-80-B10**

How to order (Zinc die casting)	
1	Length l
2	s (d <sub>1</sub> )

**GN 471.1-50-V8**