


T-nuts to swivel in



1

2

a	d				e ₁	e ₂	h ₁	h ₂	h ₃ -0,1	for slot width a
8 ^{+0,1} _{-0,1}	M 4	M 5	M 6	M 8	16	11,5	5,8	8,5	1	8
10 ^{-0,1} _{-0,3}	M 5	M 6	M 8	-	20,5	13,8	5,2	10,2	1,5	10

Specification

- Steel
zinc plated, blue passivated
- Spring steel sheet
Stainless Steel
 - AISI 301
 - spot-welded
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

T-Nuts GN 506.2 can be turned into position, i.e. they can be inserted at any point along the slot.

The spring washer prevents the nut from inadvertently being displaced inside the slot, which is particularly advantageous if the profile rail is arranged vertically. The outstanding feature of this design is that different slot heights can be bridged.

As an example, T-Nuts GN 506.2 can be used to fit hinges to commercially available extrusion rails.

How to order

GN 506.2-8-M6

1 a

2 d