



ELESA Original design M.543 / M.543-p

l ₁	d	GN 528.1			GN 528.4		b	h	l ₂	l ₃	l ₄	s	t min.
		Material / Color		PP	Material / Color								
94 -1	M 6	SW	OR	-	-	-	21	36	107	79	-	6	10
105 ±0,5	M 5	SW	OR	-	-	-	23	37	120	90	-	7	10
105 ±0,5	M 6	SW	OR	-	-	-	23	37	120	90	-	7	10
117 ±0,5	M 6	SW	OR	SW	SW	OR	25	38	134	102	16	7,5	12
117 ±0,5	M 8	SW	OR	-	-	-	25	38	134	102	-	7,5	12
132 ±0,5	M 8	SW	OR	-	-	-	26	45	150	116	-	8	13
179 ±0,5	M 8	SW	OR	-	SW	OR	28	51	200	160	16	9	13
179 ±0,5	M 10	SW	OR	-	-	-	28	51	200	160	-	9	13

Specification

- Plastic **PA**
Technopolymer (Polyamide)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black, RAL 9005, matte ● **SW**
- orange, RAL 2004, matte ● **OR**
- Plastic **PP**
Technopolymer (Polypropylene)
- glass fiber reinforced
- temperature resistant up to 100 °C
- black, RAL 9005, matte ● **SW**
- Bushing
Brass
- Threaded stud
Steel, zinc plated
- *Strength properties* → Page 1448 / 1449
- *Plastic characteristics* → Page 1483
- **RoHS**

Information

Cabinet U-handles GN 528.1 type PP (Polypropylene) offer indeed less mechanical and thermal features, however are of low cost. Their characteristics are sufficient for many applications.

see also...

- *Cabinet U-handles GN 728*
(Aluminum, mounting from the back or the operator's side) → Page 92

How to order (with threaded bushing)		1	Material
		2	l ₁
		3	d
		4	Color
GN 528.1 - PA - 132 - M8 - SW			

How to order (with threaded stud)		1	Material
		2	l ₁
		3	d
		4	Color
GN 528.4 - PA - 117 - M6 - SW			