



ELESA Original design B.193 p



GN 529

d ₁	d ₂		Length l						d ₃	h	k
15	M 3	M 4	6	10	16	-	-	-	11	11	8
15	M 5	-	10	16	25	-	-	-	11	11	8
18	M 5	-	10	16	25	40	-	-	13	12	9
22	M 6	-	10	16	20	25	30	40	15	14	9
25	M 6	M 8	16	25	-	-	-	-	18	18	12
30	M 8	-	16	25	40	-	-	-	24	18	12
35	M 8	-	25	40	-	-	-	-	27	23	20



GN 529.5

d ₁	d ₂		Length l						d ₃	h	k
15	M 3	M 4	6	10	16	-	-	-	11	11	8
15	M 5	-	10	16	25	-	-	-	11	11	8
18	M 5	-	10	16	25	-	-	-	13	12	9
22	M 6	-	10	16	20	25	30	-	15	14	9
25	M 6	-	16	25	-	-	-	-	18	18	12
30	M 8	-	16	25	40	-	-	-	24	18	12

Specification

- Plastic
Duroplast (PF)
- temperature resistant up to 110 °C
- black, shiny finish

- **GN 529**
Threaded stud
Steel zinc plated, blue passivated

- **GN 529.5**
Threaded stud
Stainless Steel AISI 303

- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

Information

The surface quality of the knurled screws GN 529 / GN 529.5 is of a sufficiently high standard to meet the highest requirements. The flash mark is not visible.

How to order (Threaded stud steel)

GN 529-25-M8-16

- | | |
|---|----------------|
| 1 | d ₁ |
| 2 | d ₂ |
| 3 | Length l |

How to order (Threaded stud Stainless Steel)

GN 529.5-18-M5-16

- | | |
|---|----------------|
| 1 | d ₁ |
| 2 | d ₂ |
| 3 | Length l |