



ELESA Original design VB.639 p

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub>	<b>3</b> Length l	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>
45	M 6	20	19	25	22,5
45	M 8	25	19	25	22,5
63	M 8	25	26	28	25
80	M 10	30	32	36	30
100	M 12	40	36	42	36

### Specification

- Plastic  
Technopolymer (Polyamide PA)  
- glass fiber reinforced  
- temperature resistant up to 130 °C  
- black, matte
- Threaded stud  
Steel  
zinc plated, blue passivated
- *Plastic characteristics* → Page 1483
- RoHS

### Information

GN 5330 tristar knobs have been developed for heavy duty applications. Due to its shape, higher torque can be achieved.

How to order

**GN 5330-100-M12-40**

<b>1</b>	d <sub>1</sub>
<b>2</b>	d <sub>2</sub>
<b>3</b>	Length l