



ELESA Original design VTL.

1	2	3						
d_1	d_2	Length l		d_3	d_4	h_1	h_2	t min.
50	M 10	20	50	23	27	84	62	17

Specification

- Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black, matte
- Color of the cover cap (shiny finish):
orange, RAL 2004
- Bushing
Brass
- Threaded stud
Steel
zinc plated, blue passivated
- *Plastic characteristics* → Page 1483
- RoHS

On request

- Cover cap in black color

Information

Star knobs / Star knobs with threaded stud GN 5332 are used when circumstances dictate an extended shaft.

How to order (bushing)

GN 5332-50-M10

1 d_1

2 d_2

How to order (threaded stud)

GN 5332-50-M10-50

1 d_1

2 d_2

3 Length l