



4 Type

E with cover cap
(threaded blind bore)

5 Loss protection

P with plastic ball chain

1 d_1	2 d_2	3 Length l				d_3	h_1	h_2	h_3	r	t
25	M 5	10	16	20	25	13	19	8	2,75	20	10
32	M 6	16	20	25	30	15	23	10	2,75	21	12
40	M 8	20	25	30	40	17	27	12	2,75	21,5	18
50	M 10	20	25	30	40	19	32	14	2,75	22,5	20
63	M 12	30	40	50	-	22	37	16	2,75	24	26

Specification

- Plastic
Technopolymer (Polypropylen PP)
- reinforced, shock resistant
- temperature resistant up to 60 °C
- black, matte
- Bushing
Brass
- Threaded stud
Steel zinc plated, blue passivated
- Retaining ring / Ball chain
Technopolymer (Polyacetal POM)
- Key ring
Stainless Steel
blackened
- *Plastic characteristics* → Page 1483
- **RoHS compliant**

On request

- Plastic ball chains with other lengths

Information

Star knobs with threaded stud GN 5337.13 can be captively attached to a base element with the help of a ball chain.

The star knobs are supplied ready **assembled** (with a plastic ball chain).

see also...

- *Star knobs GN 6336.13 (with loss protection)* → Page 405
- *Star knobs GN 5337.2 (with bushing)* → Page 406
- *Star knobs GN 5337.2 (with threaded stud)* → Page 407
- *More star knobs with loss protection GN 111.7* → Page 1426

How to order (Bushing)	
1 d_1	
2 d_2	
4 Type	
5 Loss protection	
GN 5337.13-40-M8-E-P	

How to order (Threaded stud)	
1 d_1	
2 d_2	
3 Length l	
5 Loss protection	
GN 5337.13-50-M10-30-P	