



1

2

2

d ₁	d ₂ Thread	s H9 Square	d ₃	d ₄	h ₁	h ₂	t
32	M 5	V 5	14	10	14	4	6
40	M 6	V 6	16	12	18	5	8
50	M 8	V 6	19	16	22	6	10
60	M 10	V 7	22	20	26	7	12

Specification

- Plastic
Technopolymer (Polyamide PA)
- Temperature resistant up to 90 °C
- Black shiny finish
- Bushing
Brass
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

Information

The use of shock proof technopolymer material for the triangular knobs GN 5341 eliminates the use of a metal bushing on the square knob.

see also...

- Star Knobs GN 5331 (Low Type) → Page 559

How to order

GN 5341-32-V5

1 d₁

2 s (d₂)

