



ELESA original design VTT-SST



Inox
Stainless
Steel



¹ d ₁	² d ₂	d ₃	h ₁	h ₂	t min.
25	M 5	12	20	10	10
32	M 6	14	23	11,5	10
40	M 8	16	27	13,5	13
50	M 10	19	30	15	17

Specification

- Plastic Technopolymer (Polyamide PA)
 - glass fiber reinforced
 - temperature resistant up to 130 °C
 - black, matte —
 - white, RAL 9002, Cleanline, matte ○ **CL**
- Bushing Stainless Steel
AISI 304
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

On request

- with bushing brass

Information

The underside of the GN 5342 tristar knobs is not recessed, which meets the requirements of a „hygienic“ version.

see also...

- *Star knobs GN 5337.5* → Page XYZ
- *Star knobs GN 5337.4* → Page XYZ

How to order (black)	
¹ ²	1 d ₁
GN 5342-40-M8	2 d ₂

How to order (Cleanline)	
¹ ² ³	1 d ₁
GN 5342-40-M8-CL	2 d ₂
	3 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

