



ELESA original design VTT-SST-p



1 d ₁	2 d ₂	3 Length l			d ₃	h ₁	h ₂ ≈
25	M 5	10	16	-	12	20	10
32	M 6	16	20	30	14	23	11,5
40	M 8	20	30	40	16	27	13,5
50	M 10	20	30	40	19	30	15

Specification

- Plastic
Technopolymer (Polyamide PA)
- glass fiber reinforced
- temperature resistant up to 130 °C
- black, matte
- Threaded stud
Stainless Steel
AISI 304
- *Plastic characteristics* → Page 1483
- *Stainless Steel characteristics* → Page 1489
- RoHS

On request

- with threaded stud steel, zinc plated

Information

The underside of the GN 5342 tristar knob is not recessed, which meets the requirements of a „hygienic“ version.

see also...

- *Star knobs GN 5337.5* → Page XYZ

How to order

GN 5342-50-M10-30

1	d ₁
2	d ₂
3	Length l