



ROSTFREI  
Inox  
Stainless  
Steel

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	<sup>3</sup> Length l			d <sub>3</sub>	h	k	t min.
20	M 5	10	16	-	14	13	8,5	8
24	M 6	16	20	25	16	15	10,5	9
28	M 8	16	20	30	18	17	12,5	10

### Specification

- Stainless Steel AISI 304
  - matte shot-blasted
  - highly polished
- *Stainless Steel characteristics* → Page 1489
- **RoHS**

<sup>4</sup>

**MT**  
**PL**

### Information

The knurling of the Stainless Steel-Knurled screws GN 535 / Knurled nuts GN 536 allows a use in an environment with hygienic requirements.

see also...

- *Stainless Steel-Knurled nuts DIN 6303* → Page 455
- *Stainless Steel-Knurled nuts DIN 466* → Page 456
- *Stainless Steel-Knurled screws DIN 464* → Page 457

How to order (Screw)

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup>  
**GN 535-28-M8-20-MT**

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Length l
4	Finish

How to order (Nut)

<sup>1</sup> <sup>2</sup> <sup>4</sup>  
**GN 536-20-M5-PL**

1	d <sub>1</sub>
2	d <sub>2</sub>
4	Finish