



ELESA Original design I.280 p

¹ d ₁	² d ₂	d ₃	l ₁	l ₂
18	M 6	15	40	16
21	M 8	17	50	16
23	M 10	19	65	16
26	M 10	21	80	16
28	M 12	22	90	16
31	M 12	25	102	16

Specification

- Plastic
Duroplast (Phenolic PF)
- temperature resistant up to 110 °C
- black, shiny finish
- Threaded stud
Steel
zinc plated, blue passivated
- *Plastic characteristics* → Page 1483
- **RoHS compliant**

Information

Fixed cylindrical handles GN 539 can equally well be used to replace ball knobs on operating levers. In that case the operating lever end will have to be fitted with a threaded stud.

The threaded stud is deeply embedded in the handle which greatly increases the strength of the plastic body.

see also...

- *Revolving handles GN 598* → Page 35
- *Cylindrical handles GN 519* → Page 52

How to order

GN 539-21-M8

¹ d₁

² d₂