



1.1

1.2

1.3

1.4

¹ d ₁	² d ₂	d ₃	d ₄	h ₁	h ₂	t min.
40	M 6	18	18,8	30,5	15	12
40	M 8	18	18,8	30,5	15	15
50	M 8	21	21,8	34	17	15
50	M 10	21	21,8	34	17	18

Specification

- Stainless Steel
 - AISI 316 L (A4)
 - matte (Ra < 0.8 μm)
 - polished (Ra < 0.8 μm)
- Sealing ring
 - hydrogenated acrylonitrile butadiene rubber (H-NBR)
 - blue
 - temperature resistant -25 °C to +150 °C
 - Hardness 85±5 Shore A
 - FDA compliant
- Elastomer characteristics → Page 1483
- Stainless Steel characteristics → Page 1489
- RoHS



MT
PL

Information

GN 5435 Stainless Steel-Star knobs are intended for use in hygiene areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish and the large corner radii prevent adherence of dirt and facilitate cleaning.

see also...

- Product family *Hygienic Design* → Page 16 / 18
- Sealing rings *Hygienic Design* GN 7600 → Page 881
- Adjustable Stainless Steel-Hand levers *Hygienic Design* GN 305 → Page 326
- Stainless Steel-Three lobe knobs *Hygienic Design* GN 5445 → Page 429

2.1

2.2

2.3

2.4

How to order	1	d ₁
	2	d ₂
	3	Finish

GN 5435-40-M8-PL