



ELESA Original design L.652 p

1.1

1.2

1.3

1.4

1		2		3				
l ₁		d	l ₂			h ₁	h ₂	s
Nominal dimension	Actual dimension							Square
40	41	M 5	16	20	-	28	18,5	13
40	41	M 6	20	25	-	28	18,5	13
55	56,5	M 6	20	25	-	33	21,5	15
55	56,5	M 8	20	25	-	33	21,5	15
67	68,5	M 8	20	25	30	37	24,5	16,5
67	68,5	M 10	20	30	-	37	24,5	16,5
80	82	M 10	20	30	-	41,5	25	20
93	94	M 12	30	-	-	46	28,5	21

Specification

- Plastic
Technopolymer (Polyamide PA)
- glass fiber re-inforced
- temperature resistant up to 130 °C
- black, matte
- Screw
Steel
zinc plated, blue passivated
- Plastic characteristics → Page 1483
- RoHS

Information

GN 563.1 T-Handle screws can be used on operating levers as well as on clamping fixtures. These handles lend themselves ideally for very high manual clamping forces.

2.1

2.2

2.3

2.4

How to order	1	l ₁
GN 563.1-55-M8-20	2	d
	3	l ₂